


# The new **Speakon® Adapter** NL4MMX

## Operating Instructions



The new **SECURE LOCK** feature of the NL4MM adapter enables to double lock the NL4FC cable connector on one side.

### Connecting:

- Ⓐ The NL4MM **LOCKING RING** has to be on the back position as shown.  
( 🔓 UNLOCKED 🔒 = visible)
- Ⓑ Insert the cable connector NL4FC ① and turn clockwise ② to lock (1<sup>st</sup> lock).
- Ⓒ Slide the NL4MM ring to the **LOCK** position (2<sup>nd</sup> lock).

### Release:

- Ⓐ Slide the NL4MM ring to **UNLOCK** position.
- Ⓑ To separate the NL4FC: Pull latch ① and turn counterclockwise ②.